

6649_Lámpara Esterilizadora UV Klas

FRONT PART

6649_Lámpara Esterilizadora UV Klas Manual de instrucciones (Esp)



Recomendamos que lea detenidamente este manual de instrucciones y lo conserve para futuras consultas.

Introducción:

Este producto emite luz ultravioleta de tipo C a una longitud de onda de 254nm. Consiste en una radiación invisible que elimina microorganismos y bacterias de las superficies, haciéndolas más seguras para su uso diario. Hay que tener en cuenta que existen muchos tipos de microorganismos y bacterias que poseen diferente resistencia a estas radiaciones de luz UV-C. Por este motivo, es necesario que cada uno requiera ser expuesto a diferentes niveles de radiación y tiempos de exposición. Los niveles de radiación emitidos no son perjudiciales para las personas, aunque se debe evitar el contacto de la misma con la piel y ojos.

Especificaciones:

- Luz UVC: 1W
- Longitud de onda: 254nm
- Voltaje: 3V
- Distancia funcionamiento: 1-2cm
- Tiempo de exposición: 30 segundos

Nota: Para un mayor grado de eficacia, prolongar el tiempo de exposición.

Funcionamiento:

Inserte 2xAAA baterías.
Mantenga pulsado el botón de encendido y desplace la lámpara por la superficie que desee tratar.

Advertencias:

1. No lo exponga a la lluvia o entornos mojados.
2. Evite caídas que le puedan generar daños serios.
3. No intente reparar la unidad por sí mismo, contacte con un especialista.
4. Para evitar riesgos, no se deshaga de él de manera inapropiada.
5. Limpíelo con un trapo seco.
6. No lo instale cerca de fuentes de calor o luz solar directa.
7. No inserte ningún objeto metálico en la unidad, existiría la posibilidad de un cortocircuito.
8. Mantenga fuera del alcance de los niños.
9. Evitar el contacto de la luz con la piel y los ojos.



El símbolo de referencia tanto en el producto como en su manual de usuario, indica que al final de la vida útil de los aparatos eléctricos y/o electrónicos, éstos deberán reciclarse por separado de sus residuos domésticos. Existen medios adecuados para recoger este tipo de material para su correcto reciclaje.
Para obtener más información, póngase en contacto con la autoridad local.



MADE IN PRC

MKTO CATAL IMPORTACIONES S.L. B04267225
Ctra. De Huerca-Óvera, s/n, 04640, Pulpi, Almería, Spain.

BACK PART

6649_UV Sterilizer Lamp Klas User manual (Eng)



It is recommended to read this user manual carefully and keep it for future reference.

Introduction:

This product emits type C ultraviolet light to a wavelength of 254nm. The light has invisible radiation which eliminates microorganisms and bacteria on surfaces, making them safer for daily use.

It is important to take into account that there are many types of microorganisms and bacteria which have different levels of resistance to radiation from UV-C light. For this reason, each type needs to be exposed to different levels of radiation for different times. The levels of radiation emitted are not harmful for humans, though contact with skin and eyes should be avoided.

Specifications:

- UVC Light: 1W
- Wavelength: 254nm
- Voltage: 3V
- Working distance: 1-2cm
- Exposure time: 30 seconds

Note: For a greater degree of efficiency, increase the exposure time.

Operation:

Insert 2xAAA batteries.
Hold down the power button and move the lamp across the surface to be treated.

Warnings:

1. Do not expose this product to rain or damp conditions.
2. Prevent this item from falling as it could cause serious damage.
3. Do not dismantle, repair or modify this product by yourself, contact an authorized specialist.
4. In order to avoid any risk, do not dispose of this product inappropriately.
5. Clean it with a dry cloth.
6. Do not place this item near sources of heat or expose to direct sunlight.
7. Do not insert any metal objects into this device as there is a risk of causing a short circuit in the unit.
8. Keep out of reach of children.
9. Avoid light contact with skin and eyes.



This symbol both in the product and its user manual indicates that at the end of the devices electrical life, it should be recycled separately from your household waste. There are adequate means to dispose of this material for proper recycling. For more information, contact your local authorities.



MADE IN PRC

MKTO CATAL IMPORTACIONES S.L. B04267225
Ctra. De Huerca-Óvera, s/n, 04640, Pulpi, Almería, Spain.